


VXS 系统，塔式，5 U，7 个插槽，可插拔 PSU

物料号

10836-060



VXS 塔式系统，适用于 7 块 VXS 板卡 6U, 160 mm。可选后部 I/O；通过可插拔 Open Frame 电源为系统供电。

认证



功能

系统符合 IEC 60297 - 3 - 101、- 102、- 103 标准以及 IEEE 1101.1、, 1101.10/11；背板, 符合 VITA 41.0、- 41.1、- 41.10、- 41.11

PSU, 兼容 19" 规格, 300 W；可选择安装第2块 PSU

Backplane VXS/VME64x4 slot VME64x, 6 U, 另有3个 VXS 有效载荷插槽，带 P0 plug, 环形连接

通过 4 个风扇散热, 从前到后冷却；通过风扇控制模块 (FCM) 控制温度

带直流工作电压显示模块, 支持风扇和温度告警

产品属性

产品类型: 系统

深度: 300mm
高度: 496.25mm
宽度: 221.45mm
电源: 250W
Net Weight: 13.5kg

其他产品详情

可应要求提供定制系统。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE