

用于嵌入式 NUC 的 Interscale, 传导冷却, 44 x 112 x 107 mm

物料号

14830-002



适用于嵌入式 NUC 主板的小尺寸机箱，带集成 EMC 屏蔽和传导冷却装置，基于创新的灵活型 nVent SCHROFF Interscale 平台构建。

认证



功能

模块化机箱由 3 个易于装配的部件组成；主体, 顶盖和前面板

符合 SDT.03 嵌入式 NUC 标准 <http://www.sget.org/standards.html>

专用于 IES MB95 嵌入式 NUC 主板的开孔 (<http://en.ies.de/>)

集成 EMC 屏蔽

带 5 mm 散热鳍片的顶盖集成散热片

刚性结构，只需两个螺钉

颜色 RAL 7016

安装了电路板安装螺柱

其他尺寸, 可提供其他开孔形状或位置, 以及丝印

产品属性

产品类型: 小尺寸机箱

产品系列: Interscale

类型: 桌面式

高度: 43.7mm

宽度: 112mm

深度: 106.5mm

材料: 铝

颜色: 煤灰色

颜色代码: RAL 7016

完成: 粉末涂层

防护等级: IP20

冷却: 导冷

包装数量: 1

Net Weight: 0.3kg

其他产品详情

仅列出的 Interscale 附件可以兼容该产品。

可根据要求提供改造或定制机箱。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE