

19" 抽屉，2 U，前面板阳极氧化

物料号

20110-062



19" 抽屉可以安装笔记本电脑、书写台面，便于操作。SCHROFF 19" 抽屉的承载能力为 15 KG，可将多种产品装配到抽屉上。

认证



功能

静态承载能力 15 千克

可选的书写台面

产品属性

机架高度: 2U

完成: 粉末涂层

包装数量: 1

正面表面处理: 阳极氧化

类型: 抽屉

材料: 钢

产品类型: 机柜/机架抽屉

静态负载: 15kg

搭配: 19" 机柜

Net Weight: 8.1kg

其他产品详情

请单独订购 19" 装配套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE