


Labrack 19 英寸开放式机架立柱，39 U

物料号

20118-742



适用于开放式或单独机架的 19" 立柱，承载能力高达 200 千克。这些 19" 立柱可以安装在移动或固定基座上。

认证



功能

固定或移动

各种机架

适用于电缆管道的附件

在实验室机架中心的指定重心处，静态承载能力为 200 千克或 150 千克（参阅技术参数表）

建议的最大机箱深度为 400 mm

产品属性

机架高度: 39U

高度: 1831mm

框架材料: 钢

包装数量: 1

符合: IEC 60297-3-100

完成: 粉末涂层

材料: 钢

产品系列: Labrack

产品类型: 机架

静态负载: 150kg

宽度: 600mm

Net Weight: 15kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE