


风扇转速控制装置（套件）

物料号

20118-900



Suitable for all AC fans and fan units (up to 300 W) with IEC 60320 C13 plug (plug

请单独订购电流输入线/电源电缆

认证



功能

外部传感器可以放置到所需的测量点

支持集电极开路输出（可参数化） – 警报输出（有源/无源） – 直流风扇（PWM 输出） – 远程显示屏（选配带前面板的数字显示屏）

安装在提供的支撑轨上

Suitable for all AC fans and fan units (up to 300 W) with IEC 60320 C13 plug (plug

简化的开关式温度调整装置（带旋钮和数字显示屏）

可根据项目要求选择电流输入线/电源电缆：SCHUKO-UTE / IEC / BS

产品属性

产品类型: 风扇控制模块

搭配: Varistar CP

材料: 塑料

Net Weight: 0.588kg

包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE