

交流风扇，230 VAC，119 x 119 x 25 mm，108 m³h

物料号

20700-001

轴流式风扇，119 mm，带交流输入。适用于 1 U 风扇盘的替换部件。



认证



功能

带连接电缆插头的 119 mm 直流风扇

产品属性

产品类型: 风扇

搭配: 19" 风扇盘

宽度: 119mm

长度: 119mm

高度: 25mm

交流电压: 230V

频率: 50/60 Hz

50 Hz 时的气流: 108m³/h
60 Hz 时的气流: 120m³/h
在 50 Hz 时的噪音等级: 34dB(A)
在 60 Hz 时的噪音等级: 38dB(A)
在 50 Hz 时的功率: 14W
在 60 Hz 时的功率: 11W
最大静压: 41Pa
环境温度: 70°C
Gross Weight: 0.338kg
包装数量: 1

其他产品详情

请单独订购连接电缆和防护格栅。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE