


适用于所有类型的连接器键控/编码屏蔽条，EN 60603，DIN 41612

物料号

20800-042



连接器编码装置可用于防止插入错误。

认证



功能

与插件单元配合使用，避免插入错误

适用于符合 EN 60603 (DIN 41612) 标准的连接器

所需的间隙为前面板宽度：4 HP：B 型, C, D, E, F, H

前面板宽度需要的空间：5 HP：E 型, G（需要间隔物元素）

如果使用 2 键/编码引脚，支持 66 键/编码

如果使用 6 键/编码引脚，支持 924 键/编码

产品属性

产品类型: 编码/键控指示器

材料: 聚对苯二甲酸丁二醇酯

包装数量: 1

Net Weight: 0.1kg

其他产品详情

对于 E 型 和 G 型连接器，始终需要间隔物。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE