


适用 IEL/IET 把手和 IEEE 导轨的编码键

物料号


20817-501



根据 IEEE

标准，导轨和把手可以通过编码避免将错误的板卡插入错误的插槽中。

认证



功能

4 个编码位置, 每个插件导轨产生 64 个编码; 为上下插件导轨编码时, 将产生 4096 个编码

插入可编码导轨的腔室, 也可安装到 IEL 或 IET 型压铸把手模块的背面

键控/编码销可防止将插件安装在错误的插槽中

产品属性

产品类型: 编码/键控指示器

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac; 框架式插入单元

类型: 编码销钉

搭配: 插箱; 仪器箱; 前面板


材料: 纤维增强型塑料

可燃性等级: UL® 94V-0

包装数量: 100

符合: EN 45545-2

Gross Weight: 0.016kg



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE