


四分之一旋转紧固件，带滚花头和开槽头，灰色；100 个

物料号

21101-849



1/4 旋转锁，支持预定义的锁定位置。

认证



功能

1/4 旋转锁，支持预定义的锁定位置

根据插槽位置识别锁定位置

抗振动，抗摇晃

数量 100 件

产品属性

颜色: 卵石灰

包装数量: 100

颜色代码: RAL 7032

深度: 20.6mm

完成: 镀镍

高度: 6mm

材料: 钢; 锌合金; 热塑性

产品类型: 硬件套件

宽度: 7mm

搭配: 前面板

紧固件类型: 滚花; 开槽头型

Net Weight: 0.15kg

其他产品详情

速卸锁扣：无需螺纹插件即可安装。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE