


PropacPRO 接地套件

物料号

21102-001



保护性接地连接符合：DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN 61010 - 1, VDE 0411 Part 1 DIN EN 61010 - 1A2, VDE 0411 Part 1/A1.

认证



功能

保护性接地连接符合：DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805 DIN EN 61010 - 1 /VDE 0411 Part 1 DIN EN 61010 - 1A2 /VDE 0411 Part 1/A1

经过 VDE 测试

DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805 DIN EN 61010 - 1/VDE 0411 part 1 DIN EN 61010 - 1A2/VDE 0411 part 1A1

产品属性

产品类型: 接地套件

产品系列: PropacPRO

类型: 接地套件

搭配: 仪器箱

包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE