

Rack Safety Plus, 3 U, 230 V AC, C20, C13/C19

物料号

21270-003



nVent SCHROFF Rack Safety Plus 是一款 19"

配电单元，可用作中央电源开关，将交流电供应给电气/电子设备。此外，它还配备了紧急停止功能。

认证



功能

带紧急停止功能的 19" 3 U 配电装置

作为中央电源开关向电气/电子装置供应交流电

400 V 三相或 230 V 单相电源输入，带熔断器

AC 输出，带多种接头，带 ON/OFF 开关

持续 AC 输出 (Service)

所有输出均受断路器保护

紧急停止功能符合 EN 60947-5-1 和 EN 60204-1 的要求，且可防止人为破坏

还可将额外的外部紧急停止按钮接入系统

产品属性

产品类型: 配电设备
搭配: Varistar CP; Novastar
功能: 紧急停止
交流输入电压: 230V
相数: 1
EMC 滤波器: 否
电涌放电器: 否
电涌限流器: 否
电流式漏电断路器: 是
断路器盖: 否
机架高度: 3U
插座类型: IEC C13
附件类型: 配电附件
Net Weight: 12kg
包装数量: 1

其他产品详情

要查看详细的可选功能配置信息及配置示例，请参考交付项目表。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE