

# Rack Safety Plus, 3 U, 230 伏交流电, CEE

## 物料号

**21270-010**



nVent SCHROFF Rack Safety Plus 是一款 19"

配电单元, 可用作中央电源开关, 将交流电供应给电气/电子设备。此外, 它还配备了紧急停止功能。

## 认证



## 功能

带紧急停止功能的 19" 3 U 配电装置

作为中央电源开关向电气/电子装置供应交流电

400 V 三相或 230 V 单相电源输入, 带熔断器

AC 输出, 带多种接头, 带 ON/OFF 开关

持续 AC 输出 (Service)

所有输出均受断路器保护

紧急停止功能符合 EN 60947-5-1 和 EN 60204-1 的要求, 且可防止人为破坏

还可将额外的外部紧急停止按钮接入系统

## 产品属性

产品类型: 配电设备

搭配: Varistar CP; Novastar

功能: 紧急停止

|                    |
|--------------------|
| 交流输入电压: 230V       |
| 相数: 1              |
| EMC 滤波器: 否         |
| 电涌放电器: 是           |
| 电涌限流器: 是           |
| 电流式漏电断路器: 是        |
| 断路器盖: 是            |
| 机架高度: 3U           |
| 插座类型: IEC C13      |
| 附件类型: 配电附件         |
| Net Weight: 12.5kg |
| 包装数量: 1            |

其他产品详情

要查看详细的可选功能配置信息及配置示例，请参考交付项目表。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会导致产品故障、财产损失、严重的个人伤害甚至死亡和/或使您很依赖服务中断。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE