

Rack Safety Plus, 3 U, 400 伏交流电, 32 A, CEE

物料号

21270-032



nVent SCHROFF Rack Safety Plus 是一款 19 英寸配电装置，可用作中央电源开关，将交流电供应给电气或电子装置。此外，它还配备了紧急停止功能。

功能

带紧急停止功能的 19 英寸 3 U 配电装置

作为中央电源开关向电气或电子装置供应交流电

230 / 400 V 3 相 32 A 电源输入，带电源断路器

AC 输出，带多种接头，带 ON/OFF 开关

持续 AC 输出 (Service)

所有输出均受断路器保护

紧急停止功能符合 EN 60947-5-1 和 EN 60204-1 的要求，且可防止人为破坏

还可将额外的外部紧急停止按钮接入系统

产品属性

产品类型: 配电设备

附件类型: 配电附件

断路器盖: 是

EMC 滤波器: 否

功能: 紧急停止

交流输入电压: 400V

电涌限流器: 否
相数: 3
机架高度: 3U
电流式漏电断路器: 是
插座类型: CEE; IEC C19
电涌放电器: 是
搭配: Varistar; Varistar CP; Novastar

其他产品详情

要查看详细的可选功能配置信息及配置示例，请参考交付项目表。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE