


适合螺栓固定到侧板的 EuropacPRO 盖板，SNCF，84 HP，55 mm

物料号

21500-038



盖板用于提供电磁屏蔽或机械保护。盖板可用螺钉固定在侧面板上。可根据 SNCF 用于铁路插槽。

认证



功能

适用于水平横梁的可变位置，例如标准规格的 PCB

开孔率 58%

适合与所有水平导轨搭配使用

产品属性

机架宽度: 84HP

深度: 55mm

包装数量: 2

完成: 钝化
材料: 铝
产品系列: EuropacPRO
产品类型: 盖板
类型: 穿孔
搭配: 插箱
Net Weight: 0.23kg
包装单位: 对
扭矩: 2.1N • m

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE