


CPCI 电源背板，带 P 47 连接器，6 U，8 HP，2x P47

物料号

23098-396



适用 CompactPCI 应用的电源背板。带 P47 电源连接器。

认证



功能

符合：PICMG 2.11 R1.0 CompactPCI 电源接口技术参数

符合：PICMG 2.9 R1.0 系统管理总线技术参数

单柜, 支持并行或冗余操作

地理地址可调

通过插入到插头的压接触点供电, 背板无电源电压

电源线可作为附件提供

带有电源柱的直流插座，电压降极低

产品属性

产品类型: 背板

插槽数: 1
机架高度: 6U
背板类型: CompactPCI 电源背板, 带 P47 插座
槽宽: 8HP
电源连接器类型: (2) P47
多功能连接器类型: SMCQ, 12 针; MicroMatch, 10 针
宽度: 39.6mm
Gross Weight: 0.391kg
包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE