

水平横梁绝缘条，28 HP，PC


物料号

24560-828



此绝缘条可用于背板的绝缘，或用于将金属板安装为连接器的支撑。与 L-ST 和 H-ST 水平轨道结合使用，在插箱中为插入装置创造标准化的安装深度。适用于 RatiopacPRO/-AIR、Propac Pro、CompacPRO 和 EuropacPRO/-Rugged。

认证



功能

用于背板的绝缘安装，或用于将金属板安装为连接器的支撑

与 L-ST 和 H-ST 水平横梁配合使用，为面板单元创建标准化的安装深度

产品属性

机架宽度: 28HP

包装数量: 10

可燃性等级: UL® 94V-0

长度: 144.2mm

材料: 聚碳酸酯

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

产品类型: 绝缘条

搭配: 插箱; 仪器箱

Gross Weight: 0.03kg

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE