

AirBender, 卡片导向嵌件, 70% 阻塞率, 4HP, 160mm, 10个

物料号

24563-040



nVent SCHROFF AirBender

嵌件通过在混合阻抗环境中平衡气流, 可使每个插槽的散热效率提高高达

85%。它易于安装, 可降低风扇噪音, 同时提高整体系统性能。

功能

AirBender 卡片导向嵌件通过平衡混合空气阻抗环境中的气流, 可使每个 4HP 插槽的电子系统散热效率提高高达 85%

70% 阻塞率: AirBender

可在关键组件较少的插槽中引入额外的空气阻抗, 将气流重定向到散热关键区域, 并确保所有卡片都获得更佳的散热效果

安装简单: 只需将 AirBender 夹在 nVent SCHROFF 塑料卡片导向装置中, 然后选择性地用螺钉将其固定

通过将风扇保持在高效运行点, 有利于减少风扇产生的噪音

产品属性

产品类型: 空气挡板

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

搭配: 插箱; 仪器箱; 系统

机架宽度: 4HP

深度: 160mm

材料: 聚碳酸酯

包装数量: 10

颜色: 灰色

其他产品详情

可根据要求提供具有不同阻塞率的 AirBender。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE