


EuropacPRO Advanced EMC Plus, 双层网格顶盖和底板, 用螺钉固定到侧面板, 84 HP, 295 mm, D1 160 mm

物料号

24563-774



EMC Subrack with Cover with Mesh

A cover plate is used for electromagnetic shielding and as mechanical protection. The cover can be screwed onto the side panel.

功能

双层网格顶盖和底板带有 EMC 和气流优化穿孔, 适用于最高的射频屏蔽要求

满足防火安全标准 EN 62368-1 的要求

适用于具有标准格式的 PCB

适合以螺栓固定到侧面板的盖板

适合与所有水平导轨搭配使用, 不仅仅是坚固

产品属性

深度: 295mm

包装数量: 2

完成: 钝化

材料: 铝

产品系列: EuropacPRO

产品类型: 盖板

机架宽度: 84HP

类型: 穿孔

搭配: 插箱

板深度: 160mm

包装单位: 对

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE