

CPCI Serial R3.0 系统，带可插拔 PSU，4 U，9 插槽，带后 I/O

物料号

24579-451



4 U CompactPCI Serial R3.0 系统，带垂直卡槽，适用于 9 个 3 U 规格板卡和 1 个 3 U 可插拔电源。

功能

系统符合 IEC 60297 - 3 - 101、- 102、- 103；IEEE 1101.1、1101.10/11；背板符合 PICMG CPCI - S.0 R3.0

支持 PCIe Gen 4、10 Gbase-T、S-ATA 3 和 USB 3.2 Gen 2

以太网接口支持 10GBASE-KR 和 10GBASE-T 标准，并可实施 25GBASE-KR 标准

系统含垂直卡槽。适用 3U 规格板卡

9 槽背板，3U CompactPCI Serial（单星以太网拓扑），左侧系统插槽

通过 1 U 热插拔风扇单元散热

空气滤网结构支持定制

产品属性

产品类型: 系统

插槽数: 9

类型: 19" 机架安装

背板类型: 3 U CompactPCI Serial，以太网星型

数据传输: PCIe Gen4
每插槽的功率: 40W
交流输入电压: 100 – 240V
气流方向: 从下至上
机架高度: 4U
电源类型: (2) 可插拔 PSU
包含电源: 是
后部 I/O: 是
符合: PICMG CPCI-S.0 R3.0
深度: 275mm
高度: 177mm
机架宽度: 84HP
槽宽: 4HP
系统插槽: 左

其他产品详情

可直接下单采购标准品型号，也可应要求提供其他配置。

警告

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE