


适于 70 mm 柔性热导体 (FHC) 的 Interscale 安装支架，AMD CPU

物料号

24830-003



安装支架有助于用户装配英特尔或 AMD 处理器。

认证



功能

专为使用 Intel Core-i 处理器和 AMD 处理器的 ATX/ITX/Mini ITX 和 COM 产品而设计，适用于如下插口：Intel：LGA775, LGA1150, LGA1155, LGA1156, LGA1366, LGA2011；AMD：AM2, AM2(+), AM3, AM3(+), FM1, FM2, FM2(+)

使用排除区域来避免干扰其他电路板组件

用于将 70 mm 柔性热导体装配在 CPU 上

产品属性

设计特征: AMD CPU

包装数量: 1

完成: 镀锌铝

材料: 钢

产品系列: Interscale

产品类型: 支架

类型: CPU 适配器

搭配: 仪器箱

Net Weight: 0.078kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE