



水平横梁，前端，H-LD型，重型，长喙，用于 IEEE 应用，28 HP

物料号

34560-328



Combinations of horizontal rails and side panels

“+” = can be combined, “-” = combination not recommended

	Standard rail	Standard rail with IEEE handles	Standard rail with IEEE handles (for 28 HP)	Standard rail with IEEE handles (for 48 HP)
Standard rail	-	+	+	+
Standard rail with IEEE handles	+	+	+	+
Standard rail with IEEE handles (for 28 HP)	+	+	+	+
Standard rail with IEEE handles (for 48 HP)	+	+	+	+
Side panel	Light 1.1	Standard 1.1	Heavy 1.1	Super 1.1

Side panel: Light 1.1, Standard 1.1, Heavy 1.1, Super 1.1

带长喙的水平轨道可使用 IEEE 插入/拔出把手。

认证



功能

用于带 IEEE 把手的插件

长喙 (H-LD)

安装在顶部和底部

适用于 CPCI 和 VME64x 系统

铝挤压件, 阳极氧化, 接触表面导电

产品属性

机架宽度: 28HP

包装数量: 1
完成: 阳极氧化
长度: 147.32mm
材料: 铝
产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO
产品类型: 水平横梁
类型: 重型, LD
搭配: 插箱; 仪器箱

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE