


水平横梁，后部，L-MZ 型，重型，带 Z-轨道，63 HP

物料号

34560-963



Combinations of horizontal rails and side panels

				
Light x R				
Heavy x R				
Light x L				
Channel x L				
Heavy x L				
Finger x R				

MZ 型重型横梁可使用 DIN 连接器。连接器需符合 EN 60603-2 标准。

认证



功能

适合直接安装连接器，符合 EN 60603 (DIN 41612) 标准

带适应高机械负载的 Z 型轨道 (H-WZ)

铝挤压件, 阳极氧化, 接触表面导电

产品属性

机架宽度: 63HP
包装数量: 1
完成: 阳极氧化
长度: 325.12mm
材料: 铝
产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO
产品类型: 水平横梁
类型: 重型, MZ
搭配: 插箱; 仪器箱
Gross Weight: 0.137kg

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意, 交货数量会按照声明的标准包装量执行 (例如, 5 件、10 件、50 件等) 我们会将不符合规定的订购数量 (例如 2 件) 更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE