



# EuropacPRO 安装板,带盖板时使用,84 HP,220 mm 板长

# 物料号

# 34563-024







Material	HP	W	D
34563001	28	146,87	112,50
34563009	28	146,87	172,50
34563002	42	217,99	112,50
34563014	42	217,99	172,50
34563003	63	324,67	112,50
34563019	63	324,67	172,50
34563004	84	431,35	112,50
34563024	84	431,35	172,50
34563026	84	431,35	232,50
34563028	84	431,35	292,50
34563042	84	431,35	352,50
34563044	84	431,35	412,50

带盖板时使用的安装板,适用于安装和固定重型组件。全宽安装板(与插箱或系统机箱一样宽)可固定至侧面板。非全宽安装板可通过装配条固定至侧面板和水平横梁。

4,4"型和加强型导轨不能与安装板组合使用。适用轻型(L型)水平横梁凹槽的顶盖/底盖不能与安装板组合使用。

## 认证



## 功能

用于安装和固定重型组件

安装板,全宽:安装板的宽度与插箱/系统机箱一样宽,并固定在侧面板上

导轨可安装在第一和最后一个槽位置

除安装板外,还可以将 EMC 盖板安装到插箱

不能使用4.4型和"加固"型导轨

导轨可固定在首个或最后一个槽中

#### 产品属性

机架宽度: 84HP

包装数量:1

深度: 172.5mm

材料: 铝

产品系列: EuropacPRO

产品类型: 安装板

宽度: 431.35mm

搭配: 插箱

Net Weight: 0.484kg

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书,或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告,可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

#### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

#### Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

本文档由系统生成。 nVent.com/SCHROFF 3