

水平横梁，前端，R-KD 型，加固型，短舌，28 HP

物料号

34566-228



Combinations of horizontal rails and side panels

		“+” = can be combined	“-” = combination not recommended	
Horizontal rail	Standard 1.0	-	+	+
	Standard 1.5	+	+	+
	Standard 2.0	+	+	+
	Standard 2.5	+	+	+
Side panel	Light 1.0	+	+	-
	Standard 1.0	+	+	-
	Standard 1.5	+	+	-
	Standard 2.0	+	+	-

加固型水平轨道可以耐受高达 25g 的冲击和振动。

认证



功能

R-KD 型 "加固型" 水平轨道，带有 3 孔固定槽，可耐受严苛环境

铝挤压件, 阳极氧化, 接触表面导电, 带 HP 标记

产品属性

机架宽度: 28HP

包装数量: 1

完成: 阳极氧化

长度: 147.32mm

材料: 铝

产品系列: EuropacPRO

产品类型: 水平横梁

类型: 加固型, KD

搭配: 插箱

Gross Weight: 0.09kg

其他产品详情

前端没有 M4 螺纹, 无印刷, 不带安装 19" 支架的槽口。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE