


水平轨道，前端，R-LD 型，加固型，长舌，20 HP

物料号

34566-320



Combinations of horizontal rails and side panels

	Light 1 L	Standard 2	Heavy 3 H	Rugged 4 R
Standard 1 S	-	+	+	+
Heavy 2 H	+	+	+	+
Light 3 L	+	+	-	-
Standard 4 S	+	+	-	-

Legend: + can be combined, - combination not recommended

加固型水平轨道可以满足最大 25g 的冲击和振动。它使用 IEEE 把手。

认证



功能

R-LD 型 "加固型" 水平轨道，带 3 孔固定槽，可耐受更严苛环境.

适合安装/拔出 CompactPCI 或, VME64x 规格单板

28 HP 以上印制 HP 标识

长度 20, 28, 40, 42, 63, 84 HP 或 1000 mm

铝挤压件, 阳极氧化, 接触表面导电, 带 HP 标记

产品属性

机架宽度: 20HP

包装数量: 1
完成: 阳极氧化
长度: 106.68mm
材料: 铝
产品系列: EuropacPRO
产品类型: 水平横梁
类型: 加固型, LD
搭配: 插箱
Net Weight: 0.03kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE