

19 英寸配电盘，6 类

物料号

60118-435



适用于 24 Cat6 跳线的 19" 配电盘。

认证



功能

符合 EN 50 173 技术参数 (07/95 版)

带快速释放紧固件，无需工具即可打开和关闭机箱

1 U 配电盘，带 24 个 RJ45 端口

用于通信网络, 符合 ISO/IEC 11801 (03/95 版)

采用双层绝缘位移技术 (LSA +/110)，易于安装

产品属性

产品类型: 拼接板

类型: 接线板，6 类

搭配: 机柜

完成: 粉末涂层

材料: 钢

Net Weight: 2.3kg

包装数量: 1

其他产品详情

请单独订购 19" 装配套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE