


适用组合安装的拼接件，挤压成型 6 U

物料号

64560-010



支撑装置用螺栓固定在水平横梁的网格孔中，可将 6 U 插箱拆分为 2 x 3 U 部分。

认证



功能

支撑装置用螺栓固定在水平横梁的开孔中。支撑装置也可以用螺钉固定。

正面必须用 2HP 前面板覆盖

产品属性

产品类型: 安装套件

产品系列: EuropacPRO

类型: 组合式

搭配: 插箱

材料: 锌合金

机架高度: 6U

包装数量: 1

Net Weight: 0.11kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE