

单温度和湿度传感器

物料号

EA9103



适用于 nVent SCHROFF RackPower PDU
的单温度和湿度探头传感器。

功能

单温度和湿度传感器

带 2 米电缆和集成磁铁，便于安装

适用于 RackPower RP1xxx, RP2xxx, RP6xxx 系列 PDU

可热插拔，便于集成

温度测量范围：0 至 65 °C

温度测量精度：+/- 2 %

湿度测量范围：10-90% 相对湿度, 非冷凝

湿度测量精度：+/- 5 %

产品属性

产品类型: 传感器

搭配: RackPower

高度: 270mm

包装数量: 1

插头类型: RJ45

产品系列: Enlogic

可拆卸输入电缆: 否

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE