

基本型 PDU, EB0809, 400 VAC, 3-PH, 32 A

物料号

EB0809

Modular, compact PDU. Ultra-Low Profile Design

功能

Enlogic 基础配电装置可为机柜以及开放框架机架和壁挂式机箱提供电源

输入电压 400 VAC, 3 相

C13 和 C19 插座

1RU 铝制型材

可调节的免工具安装

产品属性

产品系列: Enlogic

类型: 基本型 PDU

产品类型: 插排

插座类型: (18) C13; (6) C19

插座数量: 24

颜色: 黑色

断路器: 16 A, 1 极, Hy-Mag

开关插座: 否

断路器数量: 6

输入电缆长度: 3m

输入电缆位置: 顶部供给

输入电压: 400V

相: 3 相星型

中断额定值: 5kAIC

最大输入功率: 22.0 kVA
电流（降额电流）: 32 A
输出电压: 200 – 240VAC
机架单元: 0U
插头类型: IEC 60309 532P6 (IP44)
计量类型: 无
可拆卸输入电缆: 否
包装数量: 1

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE