


适于背板的 EuropacPro 19 英寸插箱套件， 屏蔽型, CompactPCI

适用于背板安装的 EMC 屏蔽式插箱，适用于 CPCI 应用。



认证



功能

带 F 型（“灵活型”）侧板的插箱，适用于高插入力和抽取力的 CompactPCI 面板单元

铝结构

用于安装背板的后水平横梁，带绝缘条

内部和外部尺寸符合：IEC 60297-3-100, -101, -102, -103, -104, IEEE 1101.1, IEEE 1101.10/11

提供改造，如开孔、各种表面或尺寸

1 GHz 时，EMC 电磁屏蔽约为 40 dB, 2 GHz 时，约为 30 dB, 前提是正面覆盖屏蔽型前面板, 经测试符合 VG 95373 第 15 部分

扁平包装，节省空间

IP 20，符合 IEC 60529

“重”型水平横梁

技术参数

材料: 铝

完成: 阳极氧化; 钝化

产品类型: 插箱/机箱

EMC 屏蔽: 是

Table 1/3

物料号	机架高度	深度 (D)	后部 I/O	包装数量	用于安装	板深度
24563-152	3U	235mm		1	背板	160mm
24563-457	6U	275mm	是	1	背板	80mm, 160mm
24563-452	6U	235mm		1	背板	160mm
24563-157	3U	275mm	是	1	背板	80mm, 160mm

Table 2/3

物料号	垫片类型	包含手柄	安装	符合	机架宽度	静态负载
24563-152	织物 EMC	否	机架	IEC 60297-3-103, IEEE 1101.10	84HP	11kg
24563-457	织物 EMC	否	机架	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	84HP	11kg
24563-452	织物 EMC	否	机架	IEC 60297-3-103, IEEE 1101.10	84HP	11kg
24563-157	织物 EMC	否	机架	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	84HP	11kg

Table 3/3


物料号	快速发货
24563-152	No

物料号	快速发货
24563-457	No
24563-452	No
24563-157	No

其他产品详情

支持个性化配置: 支持较大范围高度，宽度和深度定制；根据不同应用可选多种规格导轨,内部附件和安装材料。

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE