


EuropacPRO EMC 屏蔽套件, 背板到侧板



垂直型材可在侧板和背板之间形成 EMC 触点。装配网格为 30 mm。

认证



功能

如需垂直接触, 可将支撑型材固定在插箱或机箱的侧面板上 (网格深度 30 mm)

在某些设计中, 背板可用作插箱的屏蔽后面板; 在此情况下, 需要利用后水平轨道 (L - VT 或 H-VT 型) 进行嵌入式安装, 以确保水平接触

技术参数

产品系列: EuropacPRO

产品类型: 屏蔽套件

搭配: 插箱

Table 1/1

物料号	机架高度	包装数量	长度	材料	快速发货
24561-199	3U	2	110mm	不锈钢, 铝	No
24561-499	6U	2	243.35mm	不锈钢, 铝	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE