

前面板, 平板式, 带插槽, 适用于不锈钢 EMC 垫片



前面板, 平板式, 带适用于不锈钢垫片的凹槽。

认证



功能

平板式前面板, 铝, 2.5 mm, 正面阳极氧化, 背面导电

适用于不锈钢垫片

技术参数

深度:	2.5mm
机架高度:	4U
材料:	铝
完成:	阳极氧化; 钝化
附件类型:	前面板
产品类型:	前面板
类型:	不带把手的前面板
EMC 屏蔽:	无 (可改装)

Table 1/2						
物料号	机架宽度	包装数量	安装	EMC 垫片类型	正面表面处理	反面表面处理
30846-681	42HP	1	正面螺钉安装	不锈钢	阳极氧化	导电
30846-682	63HP	1	正面螺钉安装	不锈钢	阳极氧化	导电

Table 2/2					
物料号	边缘处理	符合	高度	宽度	快速发货
30846-681	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	No
30846-682	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	319.7mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE