

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

认证



功能

新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定

稳定性显著提高, 得益于优化设计和高质量材料 (PC)

提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3

“无卤素”, 符合 IEC 61249-2-21 标准

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中

可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求

可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点

存储温度：从 -40 °C.. 130 °C

技术参数

搭配: 插槽; 仪器箱; 19" 机箱; 系统

类型: 编码

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac

产品类型: 导轨

Table 1/2

物料号	材料	颜色	包装数量	板深度	槽宽	符合
64568-089	纤维增强型塑料	红色	1	160mm	2	EN 45545-2
64568-090	纤维增强型塑料	灰色	1	160mm	2	EN 45545-2
64568-109	纤维增强型塑料 , 铝	红色, 银色	1	160mm	2.5	EN 45545-2
64568-110	纤维增强型塑料 , 铝	灰色, 银色	1	160mm	2.5	EN 45545-2
24568-357	纤维增强型塑料	红色	10	70mm	2	EN 45545-2
24568-360	纤维增强型塑料	灰色	10	70mm	2	EN 45545-2
24568-358	纤维增强型塑料	灰色	10	160mm	2	EN 45545-2
24568-356	纤维增强型塑料	红色	10	160mm	2	EN 45545-2
24568-341	纤维增强型塑料 , 铝	灰色, 银色	10	280mm	2.5	EN 45545-2
24568-331	纤维增强型塑料 , 铝	红色, 银色	10	280mm	2.5	EN 45545-2
24568-332	纤维增强型塑料 , 铝	红色, 银色	10	340mm	2.5	EN 45545-2
24568-342	纤维增强型塑料 , 铝	灰色, 银色	10	340mm	2.5	EN 45545-2
64568-085	纤维增强型塑料	红色	1	70mm	2	EN 45545-2
64568-086	纤维增强型塑料	灰色	1	70mm	2	EN 45545-2
64568-091	纤维增强型塑料	红色	1	220mm	2	EN 45545-2

物料号	材料	颜色	包装数量	板深度	槽宽	符合
64568-092	纤维增强型塑料	灰色	1	220mm	2	EN 45545-2
64568-111	纤维增强型塑料 , 铝	红色, 银色	1	220mm	2.5	EN 45545-2
64568-112	纤维增强型塑料 , 铝	灰色, 银色	1	220mm	2.5	EN 45545-2

Table 2/2		
物料号	完成	快速发货
64568-089		No
64568-090		No
64568-109		No
64568-110		No
24568-357		No
24568-360		No
24568-358		No
24568-356		No
24568-341	阳极氧化	No
24568-331	阳极氧化	No
24568-332	阳极氧化	No
24568-342		No

物料号	完成	快速发货
64568-085		No
64568-086		No
64568-091		No
64568-092		No
64568-111		No
64568-112		No

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE