

Interscale for Mini-ITX, 传导散热



紧凑型机箱，集成 EMC 屏蔽和传导冷却功能，适用于 Mini-ITX 主板，基于创新且灵活的 nVent SCHROFF Interscale 平台构建。

认证



功能

模块化机箱由 3 个易于装配的部件组成；主体, 顶盖和前面板

适用于 Mini ITX I/O 面板的开孔, 电源连接器 (Phoenix Contact, 0710028) 和电源开关 (Schurter, MCS 18 Front)

集成 EMC 屏蔽

其他尺寸, 可提供其他开孔形状或位置, 以及丝印

刚性结构, 只需四个螺钉

安装了电路板安装螺柱

颜色 RAL 7016

技术参数

高度:	94mm
深度:	189mm
材料:	铝
类型:	桌面式
产品系列:	Interscale

防护等级: IP30
颜色代码: RAL 7016
产品类型: 小尺寸机箱

Table 1/2						
物料号	设计特征	包装数量	冷却	颜色	完成	宽度
14830-005	10 mm 散热片	1	导冷	煤灰色	粉末涂层	184mm
14830-006	20 mm 散热片	1	导冷	煤灰色	粉末涂层	184mm

Table 2/2	
物料号	快速发货
14830-005	No
14830-006	No

其他产品详情

仅列出的 Interscale 附件可以兼容该产品。

可根据要求提供改造或定制机箱。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE