

# LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

## 认证



## 功能

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

## 技术参数

产品类型: 灯

Table 1/3

| 物料号   | 交流输入电压   | 附件类型 | 直流输入电压  | 长度    | 包装数量 | 颜色 |
|-------|----------|------|---------|-------|------|----|
| 57274 | 250V max | 灯    |         |       | 1    | 黑色 |
| 57275 |          | 灯    |         |       | 2    | 黑色 |
| 57265 | 230V max | 灯    | 24V max | 396mm | 1    | 黑色 |

| 物料号   | 交流输入电压   | 附件类型 | 直流输入电压 | 长度     | 包装数量 | 颜色 |
|-------|----------|------|--------|--------|------|----|
| 57272 | 250V max | 灯    |        | 3000mm | 1    | 黑色 |
| 57273 | 250V max | 灯    |        | 1000mm | 1    | 黑色 |

Table 2/3

| 物料号   | 深度   | 完成   | 高度   | 材料 | 类型                     | 宽度    |
|-------|------|------|------|----|------------------------|-------|
| 57274 | 14mm | 平滑哑光 | 53mm | 塑料 | Cabinet Light,<br>接线端子 | 18mm  |
| 57275 | 4mm  | 平滑哑光 | 30mm |    | Cabinet Light,<br>磁铁   | 12mm  |
| 57265 | 40mm | 平滑哑光 |      | 塑料 | Cabinet Light          | 33mm  |
| 57272 |      | 平滑哑光 |      | 塑料 | 连接电缆                   | 0.3mm |
| 57273 |      | 平滑哑光 |      | 塑料 | Cabinet Light          |       |

Table 3/3

| 物料号   | 色温    | 标称电压 | 工作温度        | 重量     | 认证       | 快速发货 |
|-------|-------|------|-------------|--------|----------|------|
| 57274 |       | 250V | 60°C min    | 0.07kg |          | No   |
| 57275 |       |      |             | 0.08kg |          | No   |
| 57265 | 5800K | 230V | -20 to 55°C | 0.24kg | CE, RoHS | No   |
| 57272 |       | 250V | 60°C min    |        |          | No   |
| 57273 |       | 250V | 60°C min    | 0.3kg  |          | No   |

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

## North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



我们强大的品牌组合:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**