

LHX+ Control Unit



控制单元可进一步丰富 LHX+ 功能。它与 LHX+ 传感器和电动冷却器阀 23130-607 连接。这使冷却器能够根据冷却（供应）空气温度设定点控制冷却空气流量。它同时可以提供高级远程监控功能和各种设置功能。

功能

基于冷却（供应）空气温度设定值进行冷却剂流量控制。水控制套件提供更多控制功能

独立, 紧凑型 19"控制单元, 机柜上部无松散电线

清晰标记的即插即用传感器连接

技术参数

机架高度: 2U

产品类型: 控制器

材料: 钢

Table 1/2

物料号	高度	深度	搭配	包装数量	颜色	颜色代码
23130-668	88mm	220mm	Varistar, Varistar CP	1	暗灰色	RAL 7021
23130-664	88mm	220mm	Varistar, Varistar CP	1	暗灰色	RAL 7021

Table 2/2

物料号	完成	交流输入电压	宽度	快速发货
23130-668	镀锌铝	230V	439.5mm	No

物料号	完成	交流输入电压	宽度	快速发货
23130-664	镀锌铝	100 – 260V	439.5mm	No

其他产品详情

可选外部显示屏。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE