

显示器, 键盘, 触摸板, 1 U 抽屉



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

认证



功能

伸缩式 17" TFT 彩色显示器机箱, 1 U (分辨率 1280 x 1024; 可连接至 VGA 接口)

带不同语言键盘布局的键盘 (通过 USB 连接)

集成触摸板 (通过 USB 连接)

电源电压: 支持宽幅电压输入 (额定电源电压 110 至 240 VAC), 输出电压应要求可选 12、24 和 48 VDC

适用于不同服务器面板, 滑轨安装间距深度可调节的安装装置 (尺寸 c = 19" 型材的间距): 尺寸 c 470 ... 740 mm

技术参数

深度: 470mm

产品类型: 机柜/机架抽屉

Table 1/2

物料号	机架高度	包装数量	颜色	颜色代码	类型	搭配
60118-580	1U	1	墨黑色	RAL 9005	监视器、键盘、 触摸板	19" 机柜

物料号	机架高度	包装数量	颜色	颜色代码	类型	搭配
60118-582	1U	1	墨黑色	RAL 9005	监视器、键盘、 触摸板	19" 机柜
60118-581	1U	1	墨黑色	RAL 9005	监视器、键盘、 触摸板	19" 机柜

Table 2/2		
物料号	键盘类型	快速发货
60118-580	QWERTY 英式	No
60118-582	AZERTY	No
60118-581	QWERTZ	No

其他产品详情

可应要求提供更多版本。带轨迹球或数字小键盘。

其他键盘布局，请参见用户手册。

✎

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE