

MTCA 导轨

适用 MicroTCA.0、MicroTCA.1 和 MicroTCA.4 的导轨。



认证



功能

导轨，适用 MicroTCA.0, MicroTCA.1 和 MicroTCA.4

无需工具即可轻松安装在 1 HP 间距的网格中；两个导轨之间的最小间距为 3 HP（Compact Size）

技术参数

Table 1/1						
物料号	类型	搭配	材料	颜色	包装数量	快速发货
20849-200	MicroTCA 通用型	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	绿色	10	No
20849-202	MicroTCA 托架集线器	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	灰色	10	No
20849-198	MicroTCA 托架集线器	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	灰色	10	No
20849-194	MicroTCA AdvancedMC	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	红色	10	No

物料号	类型	搭配	材料	颜色	包装数量	快速发货
20849-196	MicroTCA 电源	MicroTCA 系统	聚对苯二甲酸丁二醇酯	黄色	10	No
20849-201	MicroTCA 通用型	MicroTCA 系统	聚对苯二甲酸丁二醇酯	绿色	100	No
20849-195	MicroTCA AdvancedMC	MicroTCA 系统	聚对苯二甲酸丁二醇酯	红色	100	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE