

不带门和后背板的 Novastar 机柜



设计精美的铝框架机柜，非常适合一般电子、测试与测量、音频/视频和广播应用。

认证



功能

静态承载能力高达 400 千克（参阅技术参数表）

防护类型 IP 20

机柜宽度仅 553 mm

平盖板

所有支柱（正面和背面）都有 19" 开孔

颜色：RAL 7021 或颜色组合 RAL 7021/ RAL 7035

螺栓连接, 铝挤出型材的压铸框架

不带门和后面板

技术参数

框架材料: 铝

材料: 铝; 钢

产品类型: 机柜

符合: IEC 60297-3-100

Table 1/3

物料号	机架高度	框架颜色	高度	框架颜色代码	覆层材料	宽度
15230-001	9U	暗灰色	456mm	RAL 7021	钢	553mm
15230-002	12U	暗灰色	589mm	RAL 7021	钢	553mm
15230-003	12U	暗灰色	589mm	RAL 7021	钢	553mm
15230-004	16U	暗灰色	767mm	RAL 7021	钢	553mm
15230-005	16U	暗灰色	767mm	RAL 7021	钢	553mm
15230-006	20U	暗灰色	945mm	RAL 7021	钢	553mm
15230-007	20U	暗灰色	945mm	RAL 7021	钢	553mm
15230-008	20U	暗灰色	945mm	RAL 7021	钢	553mm
15230-009	25U	暗灰色	1167mm	RAL 7021	钢	553mm
15230-010	25U	暗灰色	1167mm	RAL 7021	钢	553mm
15230-011	34U	暗灰色	1567mm	RAL 7021	钢	553mm
15230-012	34U	暗灰色	1567mm	RAL 7021	钢	553mm
15230-013	38U	暗灰色	1745mm	RAL 7021	钢	553mm
15230-014	38U	暗灰色	1745mm	RAL 7021	钢	553mm
15230-015	43U	暗灰色	1967mm	RAL 7021	钢	553mm
15230-016	43U	暗灰色	1967mm	RAL 7021	钢	553mm

物料号	机架高度	框架颜色	高度	框架颜色代码	覆层材料	宽度
15230-017	47U	暗灰色	2145mm	RAL 7021	钢	553mm
15230-018	47U	暗灰色	2145mm	RAL 7021	钢	553mm
16230-001	9U	暗灰色	456mm	RAL 7021	钢	553mm
16230-002	12U	暗灰色	589mm	RAL 7021	钢	553mm
16230-003	12U	暗灰色	589mm	RAL 7021	钢	553mm
16230-004	16U	暗灰色	767mm	RAL 7021	钢	553mm
16230-005	16U	暗灰色	767mm	RAL 7021	钢	553mm
16230-006	20U	暗灰色	945mm	RAL 7021	钢	553mm
16230-007	20U	暗灰色	945mm	RAL 7021	钢	553mm
16230-008	20U	暗灰色	945mm	RAL 7021	钢	553mm
16230-009	25U	暗灰色	1167mm	RAL 7021	钢	553mm
16230-010	25U	暗灰色	1167mm	RAL 7021	钢	553mm
16230-011	34U	暗灰色	1567mm	RAL 7021	钢	553mm
16230-012	34U	暗灰色	1567mm	RAL 7021	钢	553mm
16230-013	38U	暗灰色	1745mm	RAL 7021	钢	553mm
16230-014	38U	暗灰色	1745mm	RAL 7021	钢	553mm
16230-015	43U	暗灰色	1967mm	RAL 7021	钢	553mm

物料号	机架高度	框架颜色	高度	框架颜色代码	覆层材料	宽度
16230-016	43U	暗灰色	1967mm	RAL 7021	钢	553mm
16230-017	47U	暗灰色	2145mm	RAL 7021	钢	553mm
16230-018	47U	暗灰色	2145mm	RAL 7021	钢	553mm

Table 2/3						
物料号	覆层颜色	深度	静态负载	覆层颜色代码	包装数量	完成
15230-001	暗灰色	600mm	200kg	RAL 7021	1	粉末涂层
15230-002	暗灰色	500mm	200kg	RAL 7021	1	粉末涂层
15230-003	暗灰色	600mm	200kg	RAL 7021	1	粉末涂层
15230-004	暗灰色	500mm	200kg	RAL 7021	1	粉末涂层
15230-005	暗灰色	600mm	200kg	RAL 7021	1	粉末涂层
15230-006	暗灰色	500mm	200kg	RAL 7021	1	粉末涂层
15230-007	暗灰色	600mm	200kg	RAL 7021	1	粉末涂层
15230-008	暗灰色	800mm	200kg	RAL 7021	1	粉末涂层
15230-009	暗灰色	600mm	200kg	RAL 7021	1	粉末涂层
15230-010	暗灰色	800mm	200kg	RAL 7021	1	粉末涂层
15230-011	暗灰色	600mm	400kg	RAL 7021	1	粉末涂层
15230-012	暗灰色	800mm	400kg	RAL 7021	1	粉末涂层

物料号	覆层颜色	深度	静态负载	覆层颜色代码	包装数量	完成
15230-013	暗灰色	600mm	400kg	RAL 7021	1	粉末涂层
15230-014	暗灰色	800mm	400kg	RAL 7021	1	粉末涂层
15230-015	暗灰色	600mm	400kg	RAL 7021	1	粉末涂层
15230-016	暗灰色	800mm	400kg	RAL 7021	1	粉末涂层
15230-017	暗灰色	600mm	400kg	RAL 7021	1	粉末涂层
15230-018	暗灰色	800mm	400kg	RAL 7021	1	粉末涂层
16230-001	浅灰色	600mm	200kg	RAL 7035	1	粉末涂层
16230-002	浅灰色	500mm	200kg	RAL 7035	1	粉末涂层
16230-003	浅灰色	600mm	200kg	RAL 7035	1	粉末涂层
16230-004	浅灰色	500mm	200kg	RAL 7035	1	粉末涂层
16230-005	浅灰色	600mm	200kg	RAL 7035	1	粉末涂层
16230-006	浅灰色	500mm	200kg	RAL 7035	1	粉末涂层
16230-007	浅灰色	600mm	200kg	RAL 7035	1	粉末涂层
16230-008	浅灰色	800mm	200kg	RAL 7035	1	粉末涂层
16230-009	浅灰色	600mm	200kg	RAL 7035	1	粉末涂层
16230-010	浅灰色	800mm	200kg	RAL 7035	1	粉末涂层
16230-011	浅灰色	600mm	400kg	RAL 7035	1	粉末涂层

物料号	覆层颜色	深度	静态负载	覆层颜色代码	包装数量	完成
16230-012	浅灰色	800mm	400kg	RAL 7035	1	粉末涂层
16230-013	浅灰色	600mm	400kg	RAL 7035	1	粉末涂层
16230-014	浅灰色	800mm	400kg	RAL 7035	1	粉末涂层
16230-015	浅灰色	600mm	400kg	RAL 7035	1	粉末涂层
16230-016	浅灰色	800mm	400kg	RAL 7035	1	粉末涂层
16230-017	浅灰色	600mm	400kg	RAL 7035	1	粉末涂层
16230-018	浅灰色	800mm	400kg	RAL 7035	1	粉末涂层

Table 3/3	
物料号	快速发货
15230-001	No
15230-002	No
15230-003	No
15230-004	No
15230-005	No
15230-006	No
15230-007	No
15230-008	No

物料号	快速发货
15230-009	No
15230-010	No
15230-011	No
15230-012	No
15230-013	No
15230-014	No
15230-015	No
15230-016	No
15230-017	No
15230-018	No
16230-001	No
16230-002	No
16230-003	No
16230-004	No
16230-005	No
16230-006	No
16230-007	No

物料号	快速发货
16230-008	No
16230-009	No
16230-010	No
16230-011	No
16230-012	No
16230-013	No
16230-014	No
16230-015	No
16230-016	No
16230-017	No
16230-018	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE