


PropacPRO Complete Desktop Case, 屏蔽型



nVent SCHROFF PropacPRO 机箱可为 19"

组件提供电子保护，例如面板套件和欧式板卡。铝压铸框架和型材侧面板可保证解决方案坚固耐用。此机箱包括 EMC 屏蔽（标准）。

认证



功能

桌面式机箱, 按照 IEC 60297-3-101 标准为 19" 组件预配置

屏蔽型

底板有通风孔

带有通风槽的后面板

IP 20, 符合 IEC 60529 标准

符合 DIN EN 62368-1

技术参数

静态负载:	25kg
产品类型:	仪器箱
类型:	适用安装 19" 部件的仪器箱
产品系列:	PropacPRO
EMC 屏蔽:	是

Table 1/3						
物料号	机架高度	机架宽度	深度	包装数量	可用高度	可用宽度
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-122	6U	84HP	446mm	1	245.7mm	432mm

Table 2/3						
物料号	前部框架结构	制冷选项	符合	完成	高度	材料

24576-101	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-102	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-103	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-104	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-105	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-106	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-107	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-108	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-109	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-110	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-111	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-112	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-113	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-121	单段	否	IEC 60297-3-101	钝化, 粉末涂层	289mm	铝
24576-122	单段	否	IEC 60297-3-101	钝化, 粉末涂层	289mm	铝

Table 3/3			
物料号	防护等级	宽度	快速发货
24576-101	IP20	185.9mm	No

物料号	防护等级	宽度	快速发货
24576-102	IP20	185.9mm	No
24576-103	IP20	257mm	No
24576-104	IP20	257mm	No
24576-105	IP20	257mm	No
24576-106	IP20	363.7mm	No
24576-107	IP20	363.7mm	No
24576-108	IP20	363.7mm	No
24576-109	IP20	470.3mm	No
24576-110	IP20	470.3mm	No
24576-111	IP20	470.3mm	No
24576-112	IP20	470.3mm	No
24576-113	IP20	470.3mm	No
24576-121	IP20	470.3mm	No
24576-122	IP20	470.3mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE