

PropacPRO Complete Desktop Case, 非屏蔽型



nVent SCHROFF PropacPRO 机箱可为 19"

组件提供电子保护，例如面板套件和欧式板卡。铝压铸框架和型材侧面板可保证解决方案坚固耐用。此外，还提供广泛的附件。

认证



功能

桌面式机箱, 按照 IEC 60297-3-101 标准为 19" 组件预配置

非屏蔽型

底板有通风孔

后面板带通风孔

符合 DIN EN 62368-1

技术参数

静态负载: 25kg

产品类型: 仪器箱

类型: 适用安装 19" 部件的仪器箱

EMC 屏蔽: 无 (可改装)

产品系列: PropacPRO

Table 1/3						
物料号	机架高度	机架宽度	深度	包装数量	可用高度	可用宽度
24576-001	3U	28HP	266mm	1	112.3mm	148mm
24576-002	3U	28HP	326mm	1	112.3mm	148mm
24576-003	3U	42HP	266mm	1	112.3mm	219mm
24576-004	3U	42HP	326mm	1	112.3mm	219mm
24576-005	3U	42HP	386mm	1	112.3mm	219mm
24576-006	3U	63HP	266mm	1	112.3mm	326mm
24576-007	3U	63HP	326mm	1	112.3mm	326mm
24576-008	3U	63HP	386mm	1	112.3mm	326mm
24576-009	3U	84HP	266mm	1	112.3mm	432mm
24576-010	3U	84HP	326mm	1	112.3mm	432mm
24576-011	3U	84HP	386mm	1	112.3mm	432mm
24576-012	3U	84HP	446mm	1	112.3mm	432mm
24576-013	3U	84HP	506mm	1	112.3mm	432mm
24576-021	6U	84HP	326mm	1	245.7mm	432mm
24576-022	6U	84HP	446mm	1	245.7mm	432mm

Table 2/3						
物料号	前部框架结构	制冷选项	符合	完成	高度	材料

24576-001	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-002	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-003	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-004	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-005	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-006	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-007	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-008	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-009	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-010	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-011	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-012	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-013	单段	否	IEC 60297-3-101	钝化, 粉末涂层	155.5mm	铝
24576-021	单段	否	IEC 60297-3-101	钝化, 粉末涂层	289mm	铝
24576-022	单段	否	IEC 60297-3-101	钝化, 粉末涂层	289mm	铝

Table 3/3			
物料号	防护等级	宽度	快速发货
24576-001	IP20	185.9mm	No

物料号	防护等级	宽度	快速发货
24576-002	IP20	185.9mm	No
24576-003	IP20	257mm	No
24576-004	IP20	257mm	No
24576-005	IP20	257mm	No
24576-006	IP20	363.7mm	No
24576-007	IP20	363.7mm	No
24576-008	IP20	363.7mm	No
24576-009	IP20	470.3mm	No
24576-010	IP20	470.3mm	No
24576-011	IP20	470.3mm	No
24576-012	IP20	470.3mm	No
24576-013	IP20	470.3mm	No
24576-021	IP20	470.3mm	No
24576-022	IP20	470.3mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE