


PropacPRO Portable Case, 非屏蔽型



nVent SCHROFF PropacPRO 机箱可为 19"

的独立电子组件提供电子保护。铝压铸框架和型材侧面板可保证解决方案坚固耐用。另外，此机箱还可以安装翻转式手提把手，是广泛的附件系列的一部分。

认证



功能

适用于单个组件的桌面式机箱

配置开孔, 可安装翻转式手提把手

可选装 EMC 屏蔽部件

底板有通风孔

IP 20, 符合 IEC 60529 标准

可接地

符合 DIN EN 62368-1

技术参数

产品类型: 仪器箱

类型: 用于安装单个电子器件的仪器箱

产品系列: PropacPRO

Table 1/3						
物料号	机架高度	机架宽度	深度	包装数量	可用高度	可用宽度
14577-123	3U	42HP	326mm	1	130mm	219mm
14577-125	3U	42HP	386mm	1	130mm	219mm
14577-143	3U	63HP	326mm	1	130mm	326mm
14577-145	3U	63HP	386mm	1	130mm	326mm
14577-163	3U	84HP	326mm	1	130mm	432mm
14577-165	3U	84HP	386mm	1	130mm	432mm
14577-223	4U	42HP	326mm	1	174mm	219mm
14577-243	4U	63HP	326mm	1	174mm	326mm
14577-245	4U	63HP	386mm	1	174mm	326mm
14577-265	4U	84HP	386mm	1	174mm	432mm

Table 2/3						
物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
14577-123	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm
14577-125	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm
14577-143	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm
14577-145	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm
14577-163	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
14577-165	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	155.5mm
14577-223	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	200mm
14577-243	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	200mm
14577-245	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	200mm
14577-265	单段	否	IEC 60297-3-101	无（可改装）	钝化, 粉末涂层	200mm

Table 3/3					
物料号	材料	防护等级	静态负载	宽度	快速发货
14577-123	铝	IP20	25kg	257mm	No
14577-125	铝	IP20	25kg	257mm	No
14577-143	铝	IP20	25kg	363.7mm	No
14577-145	铝	IP20	25kg	363.7mm	No
14577-163	铝	IP20	25kg	470.3mm	No
14577-165	铝	IP20	25kg	470.3mm	No
14577-223	铝	IP20	25kg	257mm	No
14577-243	铝	IP20	25kg	363.7mm	No
14577-245	铝	IP20	25kg	363.7mm	No
14577-265	铝	IP20	25kg	470.3mm	No

请单独订购翻转式手提把手。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE