

电源, 19", 交流/直流线性稳压器, 双路输出

线性稳压器, 适用于仅允许极低输出噪音水平的应用。



认证



功能

2 种输出电压, 电气隔离

控制精度高, 残余纹波低且干扰极低

230 VAC 电源/线路电压 (可通过电源/线路电压转换套件转换为 115 VAC)

适用医疗应用 (8 mm安全间隙)

技术参数

Table 1/3

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13105-018	19" 线性稳压器	230V	12W	2	15V	0.4A
13105-017	19" 线性稳压器	230V	10W	2	12V	0.4A
13105-022	19" 线性稳压器	230V	24W	2	12V	1A

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13105-023	19" 线性稳压器	230V	30W	2	15V	1A
13105-029	19" 线性稳压器	230V	58W	2	24V	1.2A
13105-028	19" 线性稳压器	230V	45W	2	15V	1.5A
13105-021	19" 线性稳压器	230V	14W	2	5V	1.4A
13105-027	19" 线性稳压器	230V	36W	2	12V	1.5A

Table 2/3						
物料号	电压 2	电流 2	机架高度	机架宽度	深度	包装数量
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1

Table 3/3		
物料号	认证	快速发货
13105-018	EN 62368-1, RoHS, CE	No

物料号	认证	快速发货
13105-017	EN 62368-1, RoHS, CE	No
13105-022	CE, RoHS	No
13105-023	CE, RoHS	No
13105-029	CE, RoHS	No
13105-028	RoHS, CE	No
13105-021	RoHS, CE	No
13105-027	RoHS, CE	No

其他产品详情

请单独订购前面板。

输出数据是在Ta = 0 ... 50 °C 环境下测得。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE