

PSU 19" 交流/直流, Maxpower 系列 100 W, 双路输出



Pluggable 19" Power Supplies with H15 connector for fanless applications. 具有广泛的交流输入范围和两种输出电压。

认证



功能

宽幅电压输入 90 ... 254 VAC 和 100 ... 360 VDC, 带有源功率因数校正 (PFC)

2 种输出电压

高功率密度

效率高达 80%

技术参数

Table 1/3

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13100-116	19" 开关模式	90 – 264V	102W	2	15V	3.4A
13100-114	19" 开关模式	90 – 264V	93W	2	5V	9A

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13100-115	19" 开关模式	90 – 264V	101W	2	12V	4.2A
13100-112	19" 开关模式	90 – 264V	93W	2	5V	9A

Table 2/3						
物料号	电压 2	电流 2	机架高度	机架宽度	深度	包装数量
13100-116	15V	3.4A	3U	8HP	171.93mm	1
13100-114	24V	2A	3U	8HP	171.93mm	1
13100-115	12V	4.2A	3U	8HP	171.93mm	1
13100-112	12V	4A	3U	8HP	171.93mm	1

Table 3/3		
物料号	认证	快速发货
13100-116	RoHS, CE, UR	No
13100-114	RoHS, CE, UR	No
13100-115	CE, UR, RoHS	No
13100-112	CE, CSA, RoHS	No

其他产品详情

请单独订购前面板。

电源电压 > 190 VAC 且 Ta = 0 ... 50 °C 时的输出数据。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE