

PSU 19" 交流/直流最大功率 180 W, 单柜



Pluggable 19" Power Supplies with H15 connector for fanless applications. 支持宽幅 交流输入和一路输出电压。

认证



功能

宽幅电压输入 90 ... 254 VAC 和 100 ... 360 VDC, 带有源功率因数校正 (PFC)

1 输出电压

电源信号: 输出电压正常

效率高达 87%

集成有源去耦元素, 用于支持电源冗余配置

有源均流总线 (CSB)

技术参数

Table 1/2

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13100-152	19" 开关模式	90 – 264V	165W	1	15V	11A
13100-151	19" 开关模式	90 – 264V	156W	1	12V	13A

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13100-150	19" 开关模式	90 – 264V	150W	1	5V	30A
13100-153	19" 开关模式	90 – 264V	168W	1	24V	7A

Table 2/2				
物料号	机架高度	机架宽度	包装数量	快速发货
13100-152	3U	8HP	1	No
13100-151	3U	8HP	1	No
13100-150	3U	8HP	1	No
13100-153	3U	8HP	1	No

其他产品详情

请单独订购前面板。

电源电压 > 190 VAC 且 TA = 0 ... 时的输出数据50 °C。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE