


插排, 瑞士标准



模块化、紧凑型 PDU，支持多种功能。利用 1 U x 1 U 铝机箱，PDU 可以轻松集成至带瑞士插座的机架中。

认证



功能

安装时，插排可以向四个方向旋转（90°增量）

符合 SEV.IEC 60884 标准

连接电缆 2 米，带瑞士标准插头

瑞士标准插排

安装高度 1 U

水平或垂直安装

230 V, 10 A

技术参数

长度: 438.5mm

材料: 铝; 聚酰胺

颜色: 灰色

产品类型: 插排

Table 1/2						
物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
60110-453	瑞士	10	否	230V	1	44mm
60110-454	瑞士	9	是	230V	1	44mm

Table 2/2		
物料号	完成	快速发货
60110-453	阳极氧化	No
60110-454	阳极氧化	No

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE