

插排, 美标

模块化、紧凑型 PDU，支持多种功能。利用 1 U x 1 U 铝机箱，PDU 可以轻松集成至带美标插座的机架中。



认证



功能

水平或垂直安装

安装时，插排可以向四个方向旋转（90°增量）

连接电缆 2 米, 带美标插头

带美标插座的插排

安装高度 1 U

符合 UL-498 标准

115 V, 15 A

技术参数

材料: 铝; 聚酰胺

颜色: 灰色

产品类型: 插排

Table 1/2						
物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
60110-242	美国	11	是	115V	1	44mm
60110-240	美国	11	否	115V	1	44mm
60110-241	美国	15	否	115V	1	44mm

Table 2/2			
物料号	完成	长度	快速发货
60110-242	阳极氧化	438.5mm	No
60110-240	阳极氧化	438.5mm	No
60110-241	阳极氧化	947.5mm	No

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE