

插排, Wieland® Connecting Cable

支持简单连接电流供应（例如，用于插座条）



认证



功能

不同的连接插头

支持简单连接电流供应（例如，用于插座条）

可提供不同的电缆长度

技术参数

颜色: 黑色

产品类型: 电缆

Table 1/1

物料号	长度	包装数量	完成	材料	快速发货
60110-321	2500mm	1	阳极氧化	铝, 聚酰胺	No
60110-330	2500mm	1	阳极氧化	铝, 聚酰胺	No

物料号	长度	包装数量	完成	材料	快速发货
60110-322	5000mm	1	阳极氧化	铝, 聚酰胺	No
60110-323	1000mm	1	阳极氧化	铝, 聚酰胺	No
60110-331	1000mm	1	阳极氧化	铝, 聚酰胺	No
60110-329	1000mm	1	阳极氧化	铝, 聚酰胺	No
60110-324	2500mm	1	阳极氧化	铝, 聚酰胺	No
60110-328	5000mm	1	阳极氧化	铝, 聚酰胺	No
60110-325	5000mm	1	阳极氧化	铝, 聚酰胺	No
60110-332	2500mm	1	阳极氧化	铝, 聚酰胺	No
60110-327	2500mm	1	阳极氧化	铝, 聚酰胺	No
60110-326	1000mm	1	阳极氧化	铝, 聚酰胺	No
60110-320	1000mm	1	阳极氧化	铝, 聚酰胺	No

其他产品详情

可应要求提供其他输入、输出和电缆长度。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE