

通用伸缩滑轨, 2 U

通用伸缩滑轨, 延长率 > 100 %, 承载能力高达 61 kg。



认证



功能

轨道宽度 $k = 16 \text{ mm}$, 延长部件/抽屉最大安装宽度 $w = 417 \text{ mm}$

在 19" 立柱上横向安装 (19" 平面保持不占用, 用于安装延长部件/抽屉)

全延长状态下可锁定

延长宽度 > 100 %

静态承载能力每对 46 - 61 千克

技术参数

材料: 钢

产品类型: 伸缩滑轨

完成: 镀锌

Table 1/1

物料号	长度	包装数量	静态负载	类型	快速发货
-----	----	------	------	----	------

20110-100	305mm	2	61kg	通用型	No
20110-101	356mm	2	60kg	通用型	No
20110-102	406mm	2	58kg	通用型	No
20110-105	559mm	2	52kg	通用型	No
20110-103	457mm	2	57kg	通用型	No
20110-104	508mm	2	55kg	通用型	No
20110-106	610mm	2	50kg	通用型	No
20110-107	660mm	2	48kg	通用型	No
20110-108	711mm	2	46kg	通用型	No

其他产品详情

要安装于 19" 面板上，请单独订购装配套件。通用伸缩滑轨也可以在没有附加组件的情况下安装在非标准应用中，因此也适用于 19" 机柜以外的机柜。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE