

Varistar CP Base/Plinth

底座可用于存放过剩的电缆，防止机柜底部部件被老鼠咬坏。



功能

2 支撑型材, 适用于前面和背面

静态承载能力 1000 千克

技术参数

产品类型: 机柜/机架底座

材料: 钢

Table 1/2

物料号	高度	宽度	包装数量	颜色	颜色代码	深度
24630-067	200mm	800mm	1	暗灰色	RAL 7021	
24630-034	100mm	600mm	1	暗灰色	RAL 7021	600mm
24630-065	100mm	800mm	1	暗灰色	RAL 7021	
24630-037	200mm	800mm	1	暗灰色	RAL 7021	
24630-035	100mm	800mm	1	暗灰色	RAL 7021	

物料号	高度	宽度	包装数量	颜色	颜色代码	深度
24630-066	200mm	600mm	1	暗灰色	RAL 7021	
24630-064	100mm	600mm	1	暗灰色	RAL 7021	
24630-036	200mm	600mm	1	暗灰色	RAL 7021	

Table 2/2			
物料号	完成	类型	快速发货
24630-067	粉末涂层	底座, 普通	No
24630-034	粉末涂层	底座, 穿孔	No
24630-065	粉末涂层	底座, 普通	No
24630-037	粉末涂层	底座, 穿孔	No
24630-035	粉末涂层	底座, 穿孔	No
24630-066	粉末涂层	底座, 普通	No
24630-064	粉末涂层	底座, 普通	No
24630-036	粉末涂层	底座, 穿孔	No

其他产品详情

请单独订购侧面盖板。

不能与脚轮结合使用

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE